# **Product datasheet**

Specification





# switch Acti9 iSW - 1 pole - 20 A - 250V

A9S61120

### Main

Range	Acti9
Product Name	Acti9 iSW
Product Or Component Type	Switch disconnector
Device Short Name	iSW
Device Application	Control
Poles Description	1P
Utilisation Category	AC-22A
Suitability For Isolation	Yes

## Complementary

20 A at 250 V AC 50/60 Hz
250 V AC 50/60 Hz
250 V AC 50/60 Hz conforming to EN/IEC 60669-2-4
4 kV
Toggle
ON/OFF indication and lamp
Yes
AC: 230 V 50/60 Hz
Fixed
DIN rail
2
77 mm
18 mm
70 mm
Grey
300000 cycles
30000 cycles
Tunnel type terminals - 10 mm² - rigid Tunnel type terminals - 10 mm² - flexible Tunnel type terminals - 10 mm² - flexible with ferrule
9 mm
1.2 N.m

## **Environment**

Standards	EN/IEC 60669-2-4
Ip Degree Of Protection	IP4
Pollution Degree	2
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-2050 °C
Ambient Air Temperature For Storage	-4070 °C

# **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	7.500 cm
Package 1 Length	8.000 cm
Package 1 Weight	60.500 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.500 cm
Package 2 Width	9.500 cm
Package 2 Length	22.500 cm
Package 2 Weight	763.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	9.553 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information