# **Product datasheet**

Specifications





## Vigi iC60 - earth leakage add-on block - 2P - 25A - 100mA - AC type

A9V12225

#### Main

mann	
Range	Acti9
Product Or Component Type	Add-on residual current devices
Device Short Name	Vigi iC60
Poles Description	2P
[In] Rated Current	25 A
Earth-Leakage Sensitivity	100 mA
Earth-Leakage Protection Time Delay	Instantaneous
Earth Leakage Protection Type	Туре АС
Network Type	AC
Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	230415 V AC 50/60 Hz conforming to EN/IEC 61009-1 230415 V AC 50/60 Hz conforming to EN/IEC 61009-2-1
Standards	EN/IEC 61009-1 EN/IEC 61009-2-1
9 Mm Pitches	3

### Complementary

Device Location In System	Outgoer
Residual Current Tripping Technology	Voltage independent
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-2
Range Compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 Reflex iC60
Product Compatibility	Single terminal
Local Signalling	Trip indicator
Mounting Mode	Clip-on
Mounting Support	DIN rail
Electrical Connection To Mcb	By screws
Comb Busbar And Distribution Block Compatibility	Bottom: YES
Height	91 mm
Width	63 mm

Depth	73.5 mm
Net Weight	0.165 kg
Connections - Terminals	Tunnel type terminal downside for 1 cable(s) 125 mm <sup>2</sup> rigid without cable end Tunnel type terminal downside for 1 cable(s) 116 mm <sup>2</sup> flexible without cable end Tunnel type terminal downside for 1 cable(s) 116 mm <sup>2</sup> flexible with cable end
Wire Stripping Length	14 mm for bottom connection
Tightening Torque	2 N.m bottom

### Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60947-2
Electromagnetic Compatibility	$8/20 \ \mu s$ impulse withstand, 250 A conforming to IEC 61009-1
Ambient Air Temperature For Operation	-560 °C
Ambient Air Temperature For Storage	-4085 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	7.8 cm
Package 1 Length	11.5 cm
Package 1 Weight	135 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	27
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.141 kg

#### **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations