

Product datasheet

Specifications



3ft (0.9144m) Stainless Flex Pipe Kit 1" MPT to 1" FPT Union



ACAC10011

Overview

Lead Time	Special Order - Call for Quoted Lead Times
-----------	--

General

Maximum Recommended Flowrate	1.39 l/s
Tube Material	Stainless steel
Pressure Rating	2068.43 kPa
Fluid Connection Type	NPT (female) NPT (male)
Minimum Fluid Temperature	6 °C
Maximum Fluid Temperature	13 °C
Pressure Drop Per Foot	9.02 kPa @ 1.26 l/s

Physical

Length	0.91 m
Tube Diameter	25.40 mm
Net Weight	1.36 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.7 cm
Package 1 Width	73.7 cm
Package 1 Length	73.7 cm
Package 1 Weight	5.23 kg

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope