

Product datasheet

Specifications



Multifix Plus - ceiling box - with surface cover & lighting plug E27 - 67x50 mm

ALB71842

 **Discontinued on:** 12 Dec 2016

 **Discontinued**

Main

Range Of Product	Multifix
Product Name	Multifix Plus
Product Or Component Type	Ceiling box
Device Presentation	With surface cover and lighting plug E27
Provided Equipment	Hook IPX4 DCL outlet Suspension chimney Lighting plug with E27 base Surface cover DCL plug 2P+E 6A/250 VAC
Quantity Per Set	Set of 500

Complementary

Function Available	Anti-rotation system
Number Of Gangs	1 gang
Fixing Mode	By screws and claws
Material	Steel PA (polyamide) 6.6 PS (polystyrene) ABS (acrylonitrile butadiene-styrene) PC/ABS
Mechanical Robustness	Fire resistance
Colour Tint	Box: blue (RAL 5015) Plastic part: white (RAL 9010)
Cable Entry	6 knock-outs
Drill Diameter/Depth	67 mm 50 mm
Height	71 mm
Width	71 mm
Depth	49 mm

Environment

Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP20
Fire Resistance	850 °C
Standards	IEC 61995-1 IEC 60670-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	52 cm
Package 1 Width	84 cm
Package 1 Length	86 cm
Package 1 Weight	70 kg

Contractual warranty

Warranty	18 months
----------	-----------