

Product datasheet

Specifications

Tego Dial range



DIALMOVE PROFILE L100MM

APD1M010L

⚠ Discontinued on: 19 Dec 2019

⚠ Discontinued

Main

Accessories Included With Enclosure	Straight tube
Quantity Per Set	Set of 1
Range Of Product	Tego Dial

Complementary

Cable Outer Diameter	13 mm
Colour Code	RAL 7016
Colour	Grey
Horizontal Distance	1500 mm
Length	100 mm
Material	Aluminium ABS (acrylonitrile butadiene-styrene) NBR 50-60 SHORE
Maximum Load	30 kg
Maximum Room For Connectors	60 x 25 mm
Number Of Cables	4
Permanent Permissible Load	30 kg
Maximum Permissible Distance Of Load	1600 mm
Net Weight	0.9 kg
Type Of Paint	Tinted throughout Polyester powder

Environment

Product Certifications	BV
Ip Degree Of Protection	IP44 conforming to NF C 20-010 IP55 conforming to NF C 20-010
Protective Treatment	TC

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	22.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	926 g

Contractual warranty

Warranty	18 months
----------	-----------