

Product datasheet

Specifications



AS-Interface - adjustment and diagnostics terminal - LCD 25mm

ASITERV2

ⓘ Discontinued

Main

Product Or Component Type	Adjustment and diagnostics terminal
Range Compatibility	AS-Interface cabling system
Product Specific Application	Allows addressing of AS-Interface V1 and V2.1 slaves and diagnostics
Supply	LR6 batteries

Complementary

Terminal Use	2500 addressing operations
Display Type	LCD screen
Keypad Type	Selector switch + 4 keys
Electrical Connection	Cable for XZMG1. or ASITERACC.. Infrared cable for ASITERIR1
Protection Type	Overload protection Short-circuit protection
Width	84 mm
Height	195 mm
Depth	35 mm
Net Weight	0.5 kg

Environment

Ambient Air Temperature For Operation	0...55 °C
Ambient Air Temperature For Storage	-20...55 °C
Ip Degree Of Protection	IP40

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Pvc Free

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins