

Product datasheet

Specifications



NFC cartridge fuses, TeSys GS, cylindrical 14mm x 51mm, fuse type aM, 400VAC, 50A, with striker, set of 10 parts

DF3EA50

! Discontinued

! Discontinued on: 30 Sept 2020

! End-of-service on: 7 Apr 2021

Main

Range Of Product	TeSys fuse-disconnector
Product Or Component Type	Cartridge fuse
Device Short Name	DF3
[Ue] Rated Operational Voltage	400 V AC
Fuse Size	14 x 51 mm
Fuse Type	NFC
Quantity Per Set	Set of 10

Complementary

[In] Rated Current	50 A 400 V
Fuse Curve	AM
Local Signalling	Striker
Net Weight	0.02 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	7.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	19 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins