




NFC cartridge fuses, TeSys GS, cylindrical 14mm x 51mm, fuse type gG, 500VAC, 25A, with striker, set of 10 parts

DF3EN25

(!) Discontinued on: 8 Mar 2021



#### Main

Range Of Product	TeSys fuse-disconnector
Product Or Component Type	Cartridge fuse
Device Short Name	DF3
[Ue] Rated Operational Voltage	500 V AC
[In] Rated Current	25 A 500 V
Fuse Size	14 x 51 mm
Fuse Type	NFC
Quantity Per Set	Set of 10

### Complementary

Fuse Curve	GG
Local Signalling	Striker
Net Weight	0.02 kg

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.6 cm
Package 1 Width	7.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	18 g

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>9</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

**Eu Rohs Directive** 

	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Compliant