Product datasheet

Specification





gearbox straight teeth GBX, Lexium, 120mm, reduction 40:1, 9arc.min, 230N.m

GBX120040K

Main

Range Compatibility	Lexium 62					
	Lexium 52					
	Lexium 32					
	Lexium 28					
	Lexium 32i					
	Lexium 62 ILM					
Product Or Component Type	Planetary gearbox					
Gear Box Type	Straight teeth					
Device Short Name	GBX					
Product Compatibility	BMI (70 mm, 2 motor stacks)					
	BMI (70 mm, 3 motor stacks)					
	BMH (70 mm, 2 motor stacks)					
	BMH (70 mm, 3 motor stacks)					
	BSH (70 mm, 2 motor stacks)					
	BSH (70 mm, 3 motor stacks)					
	BCH2 (100 mm, 1 motor stacks)					
	BCH2 (130 mm, 1 motor stacks)					
	SH3					
	MH3					
	ILM					
Gearbox External Diameter	120 mm					
Reduction Ratio	40:1					

Complementary

Maximum Torsional Backlash	9 arc.min							
Torsional Rigidity	13 N.m/arcmin							
Housing Colour	Black							
Housing Material	Black anodized aluminium							
Shaft Material	C 45							
Additional Information	Lubricated for life							
Service Life In Hours	30000 h at 100 rpm at 30 °C							
Mounting Position	Any position							
Efficiency	94 %							
Maximum Radial Force Fr	1500 N at 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 °C							
Maximum Axial Force Fa	2100 N at 100 rpm, during 30000 hour at 30°C							
Moment Of Inertia	1.3 kg.cm²							
Continuous Output Torque	230 N.m at 100 rpm at 30 °C							
Maximum Output Torque	368 N.m at 100 rpm at 30 °C							

Net Weight	8 kg
Input Diameter	24.0 mm

Environment

Noise Level	65 dB at 1 m, no-load			
Ip Degree Of Protection	Shaft output: IP54			
Ambient Temperature For Operation	-2590 °C			

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.000 cm
Package 1 Width	13.000 cm
Package 1 Length	13.000 cm
Package 1 Weight	7.207 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	8
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	71.264 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance




Certifications & Standards

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				

GBX120040K

Dimensions Drawings

Dimensions with Servo Motor Adaptation Kit



- (1) GBK adaptation kit
- (2) GBK adaptation kit related dimensions a1, c, Ø6, Ø7, Ø8 depend on the gearbox and servo motor combination
- Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

a2						Ø1		Ø3	Ø4	Ø5
126.5	55	50	5	28	8	115	80 h7	25 h7	M10 x 16	100

Values in in

values in in.										
a2	a3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
4.98	2.17	1.97	0.19	1.10	0.31	4.53	3.15 h7	0.98 h7	M10 x 0.63	3.94