Product datasheet

Specification





Switch disconnector fuse, TeSys GS, 3P, 30A, fuse type UL, fuse size J

GS1DU3

Main

| Range | TeSys | |
|--|--------------------------|--|
| Product Name | TeSys GS | |
| Device Short Name | GS1D | |
| Product Or Component Type | Switch-disconnector-fuse | |
| Device Application | Protection | |
| Design | Compact | |
| Poles Description | 3P | |
| Protected Poles Description | 3t | |
| Contacts Type And Composition | 3 NO | |
| [Ith] Conventional Free Air Thermal Current | 30 A (at 40 °C) | |
| [le] Rated Operational Current | 30 A | |
| Fuse Type | UL | |
| Fuse Size | J | |
| Network Type | AC DC | |
| Network Frequency | 50/60 Hz | |

Complementary

| Type Of Operating Handle | External frontal |
|--|--|
| Mounting Support | Plate Rail |
| [Ui] Rated Insulation Voltage | 690 V |
| [Uimp] Rated Impulse Withstand Voltage | 8 kV |
| Rated Operational Power In W | 15 kW at 400 V 18.5 kW at 500 V 25 kW at 690 V |
| Short-Circuit Withstand | 5.5 kA |
| Mechanical Durability | 10000 cycles |
| Electrical Durability | 6000 cycles |
| Connections - Terminals | Power circuit: lugs-ring terminals26 mm² |
| Tightening Torque | Power circuit: 3 N.m |

Environment

| Standards | CSA C22.2 No 5 | |
|---------------------------------------|--|--|
| | UL 489 | |
| Product Certifications | LOVAG LROS (Lloyds register of shipping) ASEFA | |
| Ip Degree Of Protection | IP20 conforming to IEC 60529 (with terminal cover) | |
| Ambient Air Temperature For Operation | -2070 °C | |
| Ambient Air Temperature For Storage | -4080 °C | |
| Fire Resistance | 960 °C body conforming to IEC 60695-2-1 | |
| Height | 116 mm | |
| Width | 105 mm | |
| Depth | 99 mm | |
| Net Weight | 0.7 kg | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 12.6 cm |
| Package 1 Width | 13.6 cm |
| Package 1 Length | 15.7 cm |
| Package 1 Weight | 639.0 g |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 8 |
| Package 2 Height | 30 cm |
| Package 2 Width | 30 cm |
| Package 2 Length | 40 cm |
| Package 2 Weight | 5.589 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ⊘ | Toxic Heavy Metal Free | |
| ⊘ | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |