

# Product datasheet

Specifications



Plate switch, Ultimate Low profile, 2-way, screw terminals, IP20, chrome

GU1532BBC

## Main

Range Of Product	Ultimate
Range	Ultimate
Aesthetic Name	Low profile
Product Or Component Type	Plate switch
Control Type	Rocker
Switch Function	2-way
Rated Current	16 A at 230 V AC

## Complementary

Connections - Terminals	Screw terminals
Material	Steel
Quantity Per Set	Set of 1
Number Of Gangs	3 gangs
Device Mounting	Wall mounted
Height	88 mm
Width	88 mm
Depth	15 mm

## Environment

Standards	BS EN 60669-1
Ip Degree Of Protection	IP20

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	9.3 cm
Package 1 Length	10.1 cm
Package 1 Weight	133 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	22.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	42.3 cm
Package 2 Length	50 cm
Package 2 Weight	16.843 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	115 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	289.49 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability


**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>