

# Product datasheet

Specifications



Switched socket, Ultimate Slimline, complete product, 2P, screw terminal, IP20, dark grey

GU3010DGY

## Main

Aesthetic Name	Slimline
Product Or Component Type	Switched socket
Rated Current	13 A at 230 V AC 50 Hz
Fixing Mode	By screws M3.5 x 30 mm
Colour Tint	Grey moulded matt

## Complementary

Device Presentation	Complete product
Outlet Poles Configuration	2P
Outlet Standard Description	3 pins
Outlet Standard	British
Actuator	Rocker
Number Of Gangs	1 gang
Earth Circuit	Standard earth
Pilot Light	Without neon indicator
Device Mounting	Wall mounted
Connections - Terminals	Screw terminal
Material	Urea (carbamide)
Quantity Per Set	Set of 10
Height	86 mm
Width	86 mm
Depth	30 mm

## Environment

Ip Degree Of Protection	IP20
Standards	BS 1363

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	2.8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	8.7 cm
Package 1 Weight	112 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.7 cm
Package 2 Width	18.5 cm
Package 2 Length	15.5 cm
Package 2 Weight	1.206 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	17 cm
Package 3 Width	39.5 cm
Package 3 Length	51.5 cm
Package 3 Weight	12.713 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>