

# Product datasheet

Specifications



## Ultimate Slimline - surface surface mounted box - 1 gang

GU9116

### Main

Range Of Product	Ultimate
Aesthetic Name	Slimline
Product Or Component Type	Surface mounted box
Colour Tint	White
Quantity Per Set	Set of 10

### Complementary

Device Mounting	Surface
Number Of Gangs	1 gang
Cable Entry	Knock-out
Fixing Mode	By screws
Material	Urea (carbamide)
Depth	19.4 mm
Width	87.8 mm
Height	87.8 mm
Net Weight	0.061 kg

### Environment

Standards	BS EN 60670-1
-----------	---------------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.9 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	61 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.6 cm
Package 2 Width	12.8 cm
Package 2 Length	18.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	694.1 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	200
Package 3 Height	28 cm
Package 3 Width	38.9 cm
Package 3 Length	50 cm
Package 3 Weight	14.17 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability


**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Circularity Profile	No need of specific recycling operations