

Product datasheet

Specifications



Switch module, Ultimate Screwless flat plate, 2-way, snap-on, IP20, white

GUG10IW

Main

Range Of Product	Ultimate
Range	Ultimate
Device Application	Control
Aesthetic Name	Screwless flat plate
Product Or Component Type	Switch module
Control Type	Rocker
Switch Function	2-way
Rated Current	10 AX at 230 V AC

Complementary

Connections - Terminals	Snap-on
Material	Thermoplastic
Quantity Per Set	Set of 1
Number Of Gangs	1 gang
Device Mounting	Wall mounted

Environment

Standards	BS EN 60669-1
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	2.000 cm
Package 1 Length	2.500 cm
Package 1 Weight	31.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	6.600 cm
Package 2 Width	6.500 cm
Package 2 Length	8.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	206.000 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	600
Package 3 Height	16.300 cm
Package 3 Width	45.500 cm
Package 3 Length	68.000 cm
Package 3 Weight	21.657 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

<div></div> <div>Rohs Exemption Information</div> <div>Yes</div>	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration