

Product datasheet

Specifications

Power supply, Harmony iPC, Module AC for Panl PC 12"



HMIYPMAC61

⚠ Discontinued on: 31 Dec 2016

⚠ End-of-service on: 31 Dec 2020

⚠ Discontinued - Service only

Main

Range Of Product	Harmony iPC
Product Or Component Type	Power supply
Accessory / Separate Part Category	Spare part

Complementary

Accessory / Separate Part Destination	12" Harmony Panel PC
Input Voltage	100...240 V AC at 45...65 Hz
Input Current	20 mA at 100 V AC
Output Voltage	24 V DC +/- 10 %
[In] Rated Current	5.5 A
Range Compatibility	Harmony iPC
Net Weight	0.6 kg

Environment

Ambient Air Temperature For Operation	0...55 °C
Ambient Air Temperature For Storage	-20...60 °C
Relative Humidity	5...90 % non-condensing
Ip Degree Of Protection	IP20 conforming to EN 60529
Vibration Resistance	0.5 gn (f= 9...150 Hz) 1 gn (f= 9...150 Hz) 2 gn (f= 8...200 Hz) 4 gn (f= 200...500 Hz) 1.75 mm (f= 2...9 Hz) 3.5 mm (f= 2...9 Hz) 7.5 mm (f= 2...9 Hz)
Shock Resistance	15 gn operation 11 ms 30 gn transport 6 ms 30 gn storage 6 ms

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.0 cm
Package 1 Width	17.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	33.0 cm
Package 1 Weight	900.0 g