# **Product datasheet**

Specification





Horizontal distribution length, Canalis KSA400, aluminium, 400A, fixed length 2m, 8 outlets, 3L+N+PE, white RAL9001

KSA400ED4208

#### Main

Range	Canalis	
Device Short Name	KSA	
Offer Type	Advanced	
Product Or Component Type	Busbar trunking	
Busbar Description	Horizontal distribution length	
Product Compatibility	Canalis KSA busbar trunking 400 A	
Conductors Material	Aluminium	
Busbar Trunking Polarity	3L + N + PE	
Number Of Tap-Off Outlets	8	
[le] Rated Operational Current	400 A at 35 °C	
Ip Degree Of Protection	IP55 conforming to IEC 60529	
Mounting Mode	By screws	
Dimension Type	Fix	
Length	2 m	
Colour	White (RAL 9001)	

### Complementary

Number Of Poles	4
Neutral Position	Up
Mounting Position	Horizontal
[Ue] Rated Operational Voltage	230690 V
Network Frequency	50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ui] Rated Insulation Voltage	690 V
[Icw] Rated Short-Time Withstand Current	18.8 kA
[lpk] Rated Peak Withstand Current	49.2 kA
Electrical Connection	Lubricated sliding contact
Width	54 mm
Height	146 mm
Net Weight	13.9 kg
Tap-Off Unit Interval	500 mm

Radiated Magnetic Field	1 μT	
Thermal Stress Limit	354000 kA².s	
Thdi	015 % 400 A 1533 % 315 A 33100 % 250 A	
Maximum Voltage Drop	<0.022 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.022 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.021 V with power factor = 0.7 at 50 Hz with 1A for 100 m long <0.018 V with power factor = 1 at 50 Hz with 1A for 100 m long	
Standards	IEC 61439-1 IEC 61439-6	

## **Environment**

Ik Degree Of Protection	IK08 conforming to IEC 62262
Ambient Air Temperature For Operation	35 °C (without derating) 55 °C (with derating factor)

## **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.700 cm
Package 1 Width	7.500 cm
Package 1 Length	211.000 cm
Package 1 Weight	11.000 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	20
Package 2 Height	49.500 cm
Package 2 Width	64.000 cm
Package 2 Length	220.000 cm
Package 2 Weight	232.500 kg

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>Ø</b>	Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations