Product datasheet

Specification





Horizontal transport length, Canalis KSA800, aluminium, 800A, fixed length 3m, 3L+N+PE, white RAL9001

KSA800ET430

Main

Range	Canalis	
Device Short Name	KSA	
Offer Type	Advanced	
Product Or Component Type	Busbar trunking	
Busbar Description	Horizontal transport length	
Product Compatibility	Canalis KSA busbar trunking 5001000 A	
Conductors Material	Aluminium	
Busbar Trunking Polarity	3L + N + PE	
Number Of Tap-Off Outlets	0	
[le] Rated Operational Current	800 A at 35 °C	
Ip Degree Of Protection	IP55 conforming to IEC 60529	
Mounting Mode	By screws	
Dimension Type	Fix	
Length	3 m	
Colour	White (RAL 9001)	

Complementary

Number Of Poles	4
Neutral Position	Up
Mounting Position	Horizontal
[Ue] Rated Operational Voltage	230690 V
Network Frequency	50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ui] Rated Insulation Voltage	690 V
[Icw] Rated Short-Time Withstand Current	37.4 kA
[lpk] Rated Peak Withstand Current	78.7 kA
Electrical Connection	Lubricated sliding contact
Width	113 mm
Height	146 mm
Net Weight	43.1 kg
Radiated Magnetic Field	1.12 µT

Thermal Stress Limit	1758000 kA².s
Thdi	015 % 800 A 1533 % 630 A 33100 % 500 A
Maximum Voltage Drop	<0.008 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.009 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.009 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.009 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Standards	IEC 61439-1 IEC 61439-6

Environment

Ik Degree Of Protection	IK08 conforming to IEC 62262
Ambient Air Temperature For Operation	35 °C (without derating) 55 °C (with derating factor)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17 cm
Package 1 Width	12 cm
Package 1 Length	313.75 cm
Package 1 Weight	44.1 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

9	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Product datasheet

KSA800ET430

Dimensions Drawings

Dimensions

