Product datasheet

Specification





Spacial SF bottom and top frame - 300x305 mm

NSYSFC35



Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Application	Multi-purpose
Product Or Component Type	Framework kit
For Enclosure Nominal Dimensions	- H: 2000 mm W: 300 mm D: 500 mm
Mounting Location	Bottom of vertical uprights Top of vertical uprights
Range Compatibility	Spacial rear panel Spacial side panel Spacial vertical upright
Device Composition	1 bottom frame 1 roof 1 top frame
Quantity Per Set	Set of 1

Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws - each corner of enclosure location
Height	110 mm
Width	300 mm
Depth	500 mm external:

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.0 cm
Package 1 Width	33.0 cm
Package 1 Length	53.0 cm
Package 1 Weight	13.3 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations