Product datasheet

Specification





SFX 304L stainless suitable enclosure, H2000xW800xD400mm, Scotch Brite® finish.

NSYSFX20840

Main

Range	Spacial
Product Name	Spacial SFX
Enclosure Type	Multi-purpose
Category	Suitable enclosure
Nominal Height	2000 mm
Nominal Width	800 mm
Nominal Depth	400 mm
Product Installation	Floor-standing
Device Composition	1 structure 1 locking system with handle: door 4 mounting plate bracket 1 cable gland plate 1 door with reinforcement frame

Complementary

Body Type	Rear panel integrated Single piece structure folded and welded
Door Type	Plain
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, handle with 5 mm double-bar insert
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Plain
Accessibility For Operation	Front Side
Removable Parts	Door by hinges Mounting plate bracket by screws Cable gland plate by clips
Material	Structure and door: stainless steel 304L Handle: zamak Hinge: stainless steel
Surface Finish	Enclosure: Scotch-Brite® brushed Handle: painted
Net Weight	90 kg

Environment

Standards	IEC 62208 NEMA 4X
Product Certifications	UL
Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Environmental Characteristic	Corrosive Specific hygiene

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	51.0 cm
Package 1 Width	85.0 cm
Package 1 Length	214.0 cm
Package 1 Weight	91.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations