

Product datasheet

Specifications



Pragma surface enclosure - IP40 - 1 x 13 modules - transparent door

PRA21113

⚠ Discontinued on: 30 Sept 2020

⚠ To be discontinued

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	336 mm outside:
Height	300 mm
Depth	143 mm
Nb Of 18 Mm Modules Per Row	13
Nb Of Horizontal Rows	1
Electrical Insulation Class	Class II Double insulation
Provided Equipment	1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Transparent

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	26
Total Number Of 18 Mm Modules	13
Power Dissipation In W	22 W
[In] Rated Current	63 A
Type Of Rail	DIN
Cable Entry	Cut-out plates Cable or tube Removable plates Trunking
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Door: smoked Front face: grey (RAL 7004)

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	Back part: 650 °C Front face: 650 °C Door: 650 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	42 cm
Package 1 Length	38 cm
Package 1 Weight	2.4 kg

Contractual warranty

Warranty	18 months
----------	-----------