Product datasheet

Specifications





Pragma surface enclosure - IP30 - 3 x 13 modules - without door

PRA45313

() Discontinued on: 20 Nov 2023

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	336 mm outside:
Height	600 mm
Depth	123 mm
Nb Of 18 Mm Modules Per Row	13
Nb Of Horizontal Rows	3
Electrical Insulation Class	Double insulation Class II
Provided Equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Without

Complementary

-	
Enclosure Mounting	Surface
9 Mm Pitches	26
Total Number Of 18 Mm Modules	39
Power Dissipation In W	45 W
[In] Rated Current	90 A
[Ui] Rated Insulation Voltage	400 V
Type Of Rail	DIN
Cable Entry	Cable or tube
	Trunking
	Cut-out plates
	Removable plates
Number Of Terminal Blocks	1 earth (Quick) with 24 outgoers
	1 neutral (Quick) with 24 outgoers
Distribution Block Outgoers	3 x 25 mm ² for earth
	21 x 4 mm ² for earth
	3 x 25 mm ² for neutral
	21 x 4 mm ² for neutral
Enclosure Material	Back part: technoplastic
	Front face: technoplastic
	· · · · · · · · · · · · · · · · · · ·

Enclosure: white (RAL 9016) Front face: grey (RAL 7004)

Targeted Country

Portugal

Environment

Fire Resistance	Back part: 750 °C Front face: 750 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-2560 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	42.0 cm
Package 1 Length	68.0 cm
Package 1 Weight	4.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	21
Package 2 Height	120.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	96.0 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations