Product datasheet

Specifications





Pragma surface enclosure - IP30 - 4 x 18 modules - without door

PRA52718

! Discontinued on: 11 Oct 2019

(!) Discontinued

Main

Range	Pragma	
Product Or Component Type	Enclosure	
Enclosure Type	Distribution enclosure	
Width	426 mm outside:	
Height	750 mm	
Depth	125 mm	
Nb Of 18 Mm Modules Per Row	18	
Nb Of Horizontal Rows	4	
Electrical Insulation Class	Class II Double insulation	
Provided Equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip	
Type Of Door	Without	

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	36
Total Number Of 18 Mm Modules	36
Power Dissipation In W	64 W
[In] Rated Current	125 A
Type Of Rail	DIN
Cable Entry	Cut-out plates Cable or tube Trunking Removable plates
Number Of Terminal Blocks	1 earth (Quick) with 30 outgoers 1 neutral (Quick) with 28 outgoers
Distribution Block Outgoers	1 x 25 mm² for earth 1 x 50 mm² for earth 28 x 6 mm² for earth 3 x 25 mm² for neutral 1 x 50 mm² for neutral 24 x 6 mm² for neutral
Enclosure Material	Back part: technoplastic Front face: technoplastic

Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted Country	Portugal

Environment

Fire Resistance	Back part: 750 °C Front face: 750 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	Ш
Ambient Air Temperature For Operation	-2560 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	51 cm
Package 1 Length	83 cm
Package 1 Weight	7.05 kg

Contractual warranty

Warranty 18 months

25 Apr 2024



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations