

Product datasheet

Specifications



Resi9 consumer unit 3 Row 7 Way

R9H3

⚠ Discontinued on: 4 Nov 2021

⚠ Discontinued

Main

Range	Resi9
Product Or Component Type	Consumer unit equipped
Enclosure Type	Distribution enclosure
Number Of 18 Mm Modules Per Row	13
Number Of Horizontal Rows	3
Protection Device Type	2 x miniature circuit breaker (MCB) - 1P - 10 A at 230 V - B curve 4 x miniature circuit breaker (MCB) - 1P - 20 A at 230 V - B curve 1 x miniature circuit breaker (MCB) - 1P - 32 A at 230 V - B curve 1 x miniature circuit breaker (MCB) - 1P - 63 A at 230 V - B curve 1 x residual current circuit breaker (RCCB) - 1P - 63 A at 230 V - 30 mAclass AC
Type Of Door	Plain
[In] Rated Current	63 A

Complementary

Enclosure Mounting	Surface
Type Of Rail	DIN
Enclosure Material	Self-extinguishing material
Net Weight	5000 g
Width	252 mm
Height	500 mm
Depth	147 mm

Environment

Standards	IEC 60070-24 IEC 60070-1
Fire Resistance	650 °C conforming to EN/IEC 60695-2-11
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK08
Ambient Air Temperature For Operation	-15...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	17.0 cm
Package 1 Width	26.0 cm
Package 1 Length	52.0 cm
Package 1 Weight	4.737 kg