Product datasheet

Specification





Empty control station without hinges, Harmony XAP, XB2 SL, plastic, grey, undrilled, 85x226x87mm

XAPA2100

Main

Range Of Product	Harmony XAP			
Product Or Component Type	Empty control station without hinges			
Device Short Name	XAPA			
Product Front Plate Size	85 x 226 mm			
Usable Depth	83 mm			
Number Of Cut-Out	Undrilled			
Colour Of Base Of Enclosure	Grey			
Colour Of Cover	Grey			
Material	Glass reinforced polyester			
Cable Entry	Undrilled			
Device Mounting	Flush			
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP69 conforming to NF C 20-010 IP69K			
Resistance To Chemical Agents	High resistant to acids High resistant to all solvents High resistant to bases High resistant to diesel High resistant to mineral salts High resistant to oils and greases High resistant to petrol High resistant to sea water			

Complementary

Net Weight	0.6 kg	
Flame Retardance	M3 conforming to CSTB VO conforming to UL 94	

Environment

Protective Treatment	TH TC		
Ambient Air Temperature For Storage	-4070 °C		
Ambient Air Temperature For Operation	-4070 °C		
Overvoltage Category	Class II conforming to IEC 60536 Class II conforming to NF C 20-030		
Fire Resistance	850 °C conforming to NF C 20-455 960 °C conforming to IEC 92		

26 Apr 2024 Life Is On Schneider

Packing Units

9	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.000 cm
Package 1 Width	9.000 cm
Package 1 Length	23.000 cm
Package 1 Weight	689.900 g
Unit Type Of Package 2	P06
Number Of Units In Package 2	72
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	62.680 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Dimensions Drawings

Dimensions and Fixing



- (2) $2 \times \emptyset$ 5.6 mm/4.94 in. holes, depth 12 mm/0.47 in.
- P Usable depth

а		b		G		H	
mm	in.	mm	in.	mm	in.	mm	in.
85	3.35	226	8.90	70	2.76	180	7.09