Product datasheet

Specification





Harmony XVB, Illuminated unit for modular tower lights, plastic, orange, Ø70, steady, integral LED, 24 V AC/DC

XVBL0B5

Main

Range Of Product	Harmony XVB Universal
Product Or Component Type	Complete beacon
Beacon Or Indicator Bank Unit Type	Base unit direct or tube fixing Illuminated unit
Signalling Type	Steady
Mounting Diameter	70 mm
Component Name	XVBL
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit
Light Source	Integral LED, orange
Bulb Type	Protected LED
[Us] Rated Supply Voltage	24 V AC/DC

Complementary

Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm² with cable end
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1
Nominal Voltage Limit	0.851.1 Un conforming to IEC 60947-5-1
Current Consumption	< 47 mA AC/DC
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1
Cad Overall Width	70 mm
Cad Overall Height	139 mm
Cad Overall Depth	70 mm
Terminals Description Iso N°1	(COM-1)PW (GND)GROUND
Net Weight	0.27 kg

Environment

Pollution Degree	2
Product Certifications	CCC EAC CSA C22-2 No 14 UL 508
Standards	EN/IEC 60947-5-1
Protective Treatment	TC

Ambient Air Temperature For Storage	-4070 °C
Electrical Shock Protection Class	Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140
Ip Degree Of Protection	IP65 on fixing base XVBZ0. conforming to IEC 60529 IP66 on base unit conforming to IEC 60529
Nema Degree Of Protection	Type 4X conforming to UL (indoor)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.500 cm
Package 1 Width	8.000 cm
Package 1 Length	8.000 cm
Package 1 Weight	270.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.715 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

XVBL0B5

Dimensions Drawings

Illuminated Beacon for BA 15d Bulb or LED

Dimensions



Product datasheet

XVBL0B5

Connections and Schema

Illuminated Beacon

Wiring Diagram

