# **Product datasheet**

Specifications





## Complete miniature beacon, Harmony XVD Optimum, Ø 45 mm tower light, flashing, blue, IP40, 24 V

XVDLS6B6

() Discontinued

Discontinued on: 9 Feb 2023

### Main

Range Of Product	Harmony XVD Optimum
Product Or Component Type	Complete miniature beacon
Beacon Or Indicator Bank Unit Type	Base unit direct fixing Illuminated unit
Signalling Type	Flashing
Mounting Diameter	45 mm
Component Name	XVDLS
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit
Light Source	Integral flash discharge tube, blue
Bulb Type	Flash discharge tube
[Us] Rated Supply Voltage	24 V AC/DC

### Complementary

Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm <sup>2</sup> with cable end
Cable Entry	1 entry tapped for Pg 7
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1
Current Consumption	< 145 mA DC < 90 mA AC
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1
Flash Energy	1 J
Cad Overall Width	45 mm
Cad Overall Height	104 mm
Cad Overall Depth	45 mm
Terminals Description Iso N°1	(COM-1)PW (GND)GROUND
Net Weight	0.085 kg

### Environment

Product Certifications	CSA UL
Standards	EN/IEC 60947-5-1

Protective Treatment	тс
Ambient Air Temperature For Operation	-1050 °C
Ambient Air Temperature For Storage	-4070 °C
Electrical Shock Protection Class	Class II conforming to IEC 60536
Ip Degree Of Protection	IP40 conforming to IEC 60529

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	5.6 cm
Package 1 Length	5.6 cm
Package 1 Weight	109.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	12
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.533 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**


Circularity Profile	No need of specific recycling operations
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration

### **Product datasheet**

#### **Dimensions Drawings**

#### Illuminated Beacon

#### Dimensions



## Product datasheet

Mounting and Clearance

#### Illuminated Beacon

#### Panel Cut-out for Direct Fixing

