Product datasheet

Specifications





rotating mirror beacon XVR - Ø 165 - yellow - 25 W - 24 V AC DC

XVR1B08

() Discontinued on: 1 Jul 2020

Main

Range Of Product	Harmony XVR Application
Product Or Component Type	Rotating mirror beacon
Component Name	XVR
Mounting Diameter	165 mm
Light Source	Bulb included, yellow
Bulb Type	Incandescent with BA 15d base
Power Dissipation In W	25 W
[Us] Rated Supply Voltage	24 V AC/DC

Complementary

e emprementar y	
Material	Glass reinforced polyamide 6: base unit Polycarbonate: domed lens unit
Clamping Connection Capacity	<= 1 x 1.5 mm ²
Cable Entry	1 tapped entry for cable gland (included) for M20
[Ui] Rated Insulation Voltage	250 V conforming to EN/IEC 60947-1
Current Consumption	< 1050 mA
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-1
Service Life In Hours	2000 h
Operating Position	Horizontal
Flashing Frequency	3 Hz
Cad Overall Width	165 mm
Cad Overall Height	202 mm
Cad Overall Depth	165 mm
Net Weight	1.165 kg

Environment

Standards	EN/IEC 60947-5-1 EN/IEC 60947-1 CSA C22.2 No 14 UL 508
Protective Treatment	TC
Ambient Air Temperature For Storage	-4070 °C

Ambient Air Temperature For Operation	-2050 °C
Electrical Shock Protection Class	Class I conforming to EN/IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Nema Degree Of Protection	NEMA 4X conforming to UL 508 (indoor) NEMA 4X conforming to CSA C22 (indoor)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information