

Product datasheet

Specifications



Multisound siren, Harmony XVS,
white colour, 106dB, 2tones, 230V
AC

XVS10MMW

Main

| | |
|---------------------------|---|
| Range Of Product | Harmony XVS |
| Product Or Component Type | Siren |
| Device Short Name | XVS |
| Colour | White |
| Signalling Type | 2 tones siren |
| [Us] Rated Supply Voltage | 230 V AC |
| Noise Level | 106 dB (continuous or intermittent tone) at 1 m |

Complementary

| | |
|--|---------------------|
| Material | PC: body |
| Net Weight | 1 kg |
| Marking | CE |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV |
| Current Consumption | 40 mA at 230 V |
| Clamping Connection Capacity | <= 1 x 1.5 mm² |
| Electrical Connection | Cable: 6.5...8.5 mm |
| Width | 114 mm |
| Height | 114 mm |
| Depth | 153.2 mm |

Environment

| | |
|---------------------------------------|----------------------------------|
| Standards | IEC 60947-1 IEC 60947-5-1 |
| Protective Treatment | TC |
| Ambient Air Temperature For Storage | -35...70 °C |
| Ambient Air Temperature For Operation | -30...50 °C |
| Electrical Shock Protection Class | Class II conforming to IEC 61140 |
| Ip Degree Of Protection | IP53 |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-----------|
| Package 1 Height | 19.500 cm |
| Package 1 Width | 14.000 cm |
| Package 1 Length | 14.000 cm |
| Package 1 Weight | 1.242 kg |
| Unit Type Of Package 2 | S04 |
| Number Of Units In Package 2 | 8 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 40.000 cm |
| Package 2 Length | 60.000 cm |
| Package 2 Weight | 11.109 kg |
| Unit Type Of Package 3 | P06 |
| Number Of Units In Package 3 | 32 |
| Package 3 Height | 75.000 cm |
| Package 3 Width | 60.000 cm |
| Package 3 Length | 80.000 cm |
| Package 3 Weight | 53.960 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance



Mercury Free



Rohs Exemption Information

[Yes](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)

Dimensions Drawings

Siren

Dimensions

