



selector switch head Ø22 2position stay put 5 multichips



ZB4BG4C

! Discontinued on: 1 Oct 2020

① Discontinued

Main

Range Of Product	Harmony XB4	
Product Or Component Type	Head for key selector switch	
Device Short Name	ZB4	
Bezel Material	Chromium plated metal	
Mounting Diameter	22 mm	
Head Type	Standard	
Sale Per Indivisible Quantity	1	
Shape Of Signaling Unit Head	Round	
Operator Profile	Black key switch	
Type Of Operator	Stay put	
Operator Position Information	2 positions 90°	
Type Of Keylock	Special key	
Product Compatibility	5 multi-chip	
Key Withdrawal Position	In any position	

Complementary

Device Presentation	Racic element
	C15 for <1 contacts using single blocks in front mounting
	C11 for <3 contacts using single blocks in front mounting
	C8 for <4 contacts using single and double blocks in front mounting
	C7 for <4 contacts using single blocks in front mounting
	C6 for <5 contacts using single and double blocks in front mounting
	C5 for <5 contacts using single blocks in front mounting
	C4 for <6 contacts using single and double blocks in front mounting
Electrical Composition Code	C3 for <6 contacts using single blocks in front mounting
Mechanical Durability	1000000 cycles
Resistance To High Pressure Washer	7000000 Pa at 55 °C, distance : 0.1 m
Cad Overall Depth	72 mm
Cad Overall Height	29 mm
Cad Overall Width	29 mm

Environment

Protective Treatment	тн
Ambient Air Temperature For	-4070 °C

Ambient Air Temperature For Operation	-2570 °C
Overvoltage Category	Class I conforming to IEC 60536
Ip Degree Of Protection	IP69K conforming to IEC 60529
Nema Degree Of Protection	NEMA 13 NEMA 4X
Standards	GB 14048.5 EN/IEC 60947-5-1 EN/IEC 60947-1 CSA C22.2 No 14 UL 508 EN/IEC 60947-5-4 EN/IEC 60947-5-5
Product Certifications	BV UL listed GL CSA LROS (Lloyds register of shipping) DNV
Vibration Resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6
Shock Resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	8.8 cm
Package 1 Length	3.4 cm
Package 1 Weight	69.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	1
Package 2 Height	5.4 cm
Package 2 Width	8.8 cm
Package 2 Length	3.4 cm
Package 2 Weight	69.0 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information