

# Product datasheet

Specifications



## 18M SIDE PANEL PRISMA G IP30

01044

! Discontinued on: 30 September 2022

! To be discontinued

### Main

Range	Prisma
Range of product	Prisma G
Product or component type	Side panel
Accessory / separate part category	Enclosure accessory Spare part
Range compatibility	Prisma (Prisma G) enclosure
Installation description	Wall-mounted enclosure
Mounting location	Side
Number of vertical modules [50 mm]	18

### Complementary

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Textured epoxy polyester Glossy
Colour	White (RAL 9001)
Special colour options	Yes
Width	200 mm
Height	925 mm
Depth	180 mm
Net weight	1.9 kg
Quantity per set	Set of 1

### Environment

IP degree of protection	IP30
IK degree of protection	IK07 IK08

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	5.0 cm
Package 1 Width	20.5 cm
Package 1 Length	113.0 cm
Package 1 Weight	2.09 kg
Unit Type of Package 2	P12
Number of Units in Package 2	36
Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	87.24 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	12 months
----------	-----------

## Recommended replacement(s)

01044 is replaced by:

1x



Side panel, PrismaSeT G, for enclosure H 780mm (18M), IP30  
LVS01044