

Product datasheet

Specifications



21M SIDE PANEL PRISMA G IP30

01045

! Discontinued on: 30 September 2022

! To be discontinued

Main

Range	Prisma
Range of product	Prisma G
Product or component type	Side panel
Accessory / separate part category	Enclosure accessory Spare part
Range compatibility	Prisma (Prisma G) enclosure
Installation description	Wall-mounted enclosure
Mounting location	Side
Number of vertical modules [50 mm]	21

Complementary

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Glossy Textured epoxy polyester
Colour	White (RAL 9001)
Special colour options	Yes
Width	200 mm
Height	1075 mm
Depth	180 mm
Net weight	2.22 kg
Quantity per set	Set of 1

Environment

IP degree of protection	IP30
IK degree of protection	IK07 IK08

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1

Package 1 Height	5.0 cm
Package 1 Width	20.5 cm
Package 1 Length	113.0 cm
Package 1 Weight	2.4 kg
Unit Type of Package 2	P12
Number of Units in Package 2	36
Package 2 Height	60.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	98.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	12 months
----------	-----------

Recommended replacement(s)

01045 is replaced by:

1x



Side panel, PrismaSeT G, for enclosure H 1080mm (21M), IP30
LVS01045