

# Product datasheet

Specifications



## FRONT PLATE FOR 3 1P-METERS W600 6M

03155

! Discontinued on: 18 October 2020

! End-of-service on: 20 October 2020

! Discontinued

03155 has not been replaced. Please contact your customer care centre for more information.

### Main

Range	Prisma
Range of product	Prisma G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	Prisma G enclosure
Type of front plate	Cut-out
Type of front plate	Metering
Installed device	Power meters: kilowatt-hour meters - vertical installation
Poles description	3 x 2P: mounting plate support: kilowatt-hour meters vertical installation

### Complementary

Enclosure/Cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Number of vertical modules [50 mm]	6
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA
Material	Steel
Surface finish	Smooth Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	500 mm
Width	500 mm
Net weight	2.22 kg
Quantity per set	Set of 1
Functional unit	600 mm Prisma G floor-standing enclosure power meters kilowatt-hour meters vertical 2P 3 6 600 mm Prisma G wall-mounted enclosure power meters kilowatt-hour meters vertical 2P 3 6

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.22 kg
Package 1 Height	13 cm
Package 1 width	35 cm
Package 1 Length	50 cm
Unit Type of Package 2	P12
Number of Units in Package 2	12
Package 2 Weight	32.52 kg
Package 2 Height	77 cm
Package 2 width	80 cm
Package 2 Length	120 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	12 months
----------	-----------