



! Discontinued

Commercial status

Discontinued on: 18 October 2020

End-of-service on: 20 October 2020

03168 has not been replaced. Please contact your customer care centre for more information.

Main

Range	Prisma
Range of product	Prisma G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	Prisma G enclosure
Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Installed device	Tego Power: fixed Tego Power - vertical installation
Number of vertical modules [50 mm]	4 module(s): Tego Power in 600 mm Widefloor-standing enclosure 4 module(s): Tego Power in 600 mm Widewall-mounted enclosure
Standards	IEC 61439-2
Product certifications	ASEFA

Complementary

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Smooth
Colour	White (RAL 9001)
Width	470 mm
Height	320 mm
Net weight	1.78 kg
Functional unit	600 mm Prisma G floor-standing enclosure Tego Power Tego Power fixed vertical 4 12.5 mm 600 mm Prisma G wall-mounted enclosure Tego Power Tego Power fixed vertical 4 12.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.78 kg
Package 1 Height	3 cm

Package 1 width	32.5 cm
Package 1 Length	46.5 cm
Unit Type of Package 2	S04
Number of Units in Package 2	8
Package 2 Weight	15.14 kg
Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free product

Contractual warranty

Warranty	12 months
----------	-----------