
# **Product datasheet**

Specifications

 → Green Premium<sup>™</sup>



## FRONT PLATE VIGI NSX/CVS 250 HORIZONTAL TOGGLE/ ROTARY HANDLE W600 4M

03292

() Discontinued on: 15 Jun 2023

① Discontinued

#### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma Pack 250 enclosure
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed NSX100250 and ammeter without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS100160 with earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS250 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100160 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100160 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100160 with earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX250 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX250 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX250 with earth leakage protection - control: toggle - horizontal installation Enerlin'X: fixed FDM121 - control: remote control - vertical installation
Poles Description	<ul> <li>1 x 3P: mounting plate support: CVS100160 horizontal installation</li> <li>1 x 4P: mounting plate support: CVS100160 horizontal installation</li> <li>1 x 3P: mounting plate support: CVS250 horizontal installation</li> <li>1 x 4P: mounting plate support: CVS250 horizontal installation</li> <li>1 x 4P: mounting plate support: CVS250 horizontal installation</li> <li>1 x 4P: mounting plate support: NSX100160 horizontal installation</li> <li>1 x 4P: mounting plate support: NSX100160 horizontal installation</li> <li>1 x 4P: mounting plate support: NSX250 horizontal installation</li> <li>1 x 4P: mounting plate support: NSX250 horizontal installation</li> <li>1 x 4P: mounting plate support: NSX250 horizontal installation</li> <li>1 x 4P: mounting plate support: NSX250 horizontal installation</li> <li>1 x 4P: mounting plate support: NSX250 horizontal installation</li> <li>1 x 4P: mounting plate support: NSX100250 and ammeter horizontal installation</li> <li>1 x 4P: mounting plate support: NSX100250 and ammeter horizontal installation</li> </ul>

## Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Pack enclosure - width 600 mm Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA

Surface Finish	Matt Smooth	
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Colour	White (RAL 9001)	
Height	200 mm	
Net Weight	0.8 kg	
Quantity Per Set	Set of 1	

#### **Functional Unit**

600 mm Prisma G floor-standing enclosure Enerlin'X FDM121 fixed remote control vertical 1 600 mm Prisma G wall-mounted enclosure Enerlin'X FDM121 fixed remote control

vertical 1 600 mm Prisma Pack 250 Pack enclosure Enerlin'X FDM121 fixed remote control

vertical 1 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...250 and ammeter without fixed toggle horizontal 3P 1 direct with long terminal shield 4 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...250 and ammeter without fixed toggle horizontal 3P 1 direct with long terminal shield 4 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...250 and ammeter without fixed toggle horizontal 4P 1 direct with long terminal shield 4 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...250 and ammeter without fixed toggle horizontal 4P 1 direct with long terminal shield 4 600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 600 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 600 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 600 + 300 mm Prisma G floor-standing enclosure + duct EasyPact CVS250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 600 + 300 mm Prisma G wall-mounted enclosure + duct EasyPact CVS250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 600 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 600 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 600 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 600 mm Prisma G wall-mounted enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 5 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4

600 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5

600 mm Prisma G wall-mounted enclosure ComPact NSX250 with fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 5

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 with fixed toggle horizontal 3P 1 direct with long terminal shield 4

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 with fixed

toggle horizontal 3P 1 direct with long terminal shield 4

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 with fixed toggle horizontal 4P 1 direct with long terminal shield 4

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 with fixed toggle horizontal 4P 1 direct with long terminal shield 4

## **Packing Units**

U	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	21.500 cm
Package 1 Length	52.500 cm
Package 1 Weight	800.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.000 cm
Package 2 Width	22.500 cm
Package 2 Length	53.000 cm
Package 2 Weight	8.250 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	360
Package 3 Height	82.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	319.360 kg

### **Contractual warranty**

Warranty

12 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes
 Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile