



# IP55 side panels, D = 600 mm. Package of 2 for Left/Right



! Discontinued on: 12 May 2023



### Main

| Range                     | Prisma                    |
|---------------------------|---------------------------|
| Range Of Product          | Prisma P                  |
| Product Or Component Type | Side panel                |
| Range Compatibility       | Prisma Prisma P enclosure |
| Installation Description  | Cubicle, depth 600 mm     |

## Complementary

| Protective Treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |
|----------------------|--|
| Surface Finish       | Matt<br>Smooth   |
| Width                | 600 mm   |
| Height               | 2000 mm  |
| Net Weight           | 34.18 kg   |
| Quantity Per Set     | Set of 2   |

### **Environment**

Ip Degree Of Protection IP55

## **Packing Units**

| Unit Type Of Package 1       | PCE      |
|------------------------------|----------|
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 9.0 cm   |
| Package 1 Width              | 67.0 cm  |
| Package 1 Length             | 204.4 cm |
| Package 1 Weight             | 33.6 kg  |
| Unit Type Of Package 2       | PAL      |
| Number Of Units In Package 2 | 10       |
| Package 2 Height             | 100 cm   |
| Package 2 Width              | 205 cm   |
| Package 2 Length             | 120 cm   |
| Package 2 Weight             | 341.8 kg |

## **Contractual warranty**

Warranty

12 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

| <b>②</b> | Reach Free Of Svhc             |
|----------|--------------------------------|
| <b>Ø</b> | Toxic Heavy Metal Free         |
| <b>②</b> | Mercury Free                   |
| <b>Ø</b> | Rohs Exemption Information Yes |
| <b>②</b> | Halogen Free Product           |

### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration            |
| China Rohs Regulation    | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | End of Life Information   |