Product datasheet

Specifications



MEMBRANE GLAND PLATE 25 ENTRIES DIAMETER 5-26MM PRISMA G IP30 AND IP55

08872

Main

Prisma G
Prisma
Prisma Prisma G gland plate
Gland plate
Enclosure accessory
IP43 enclosure IP31 enclosure IP55 enclosure IP30 enclosure
Wall-mounted enclosure - width 600mm Floor-standing enclosure - width 600mm Wall-mounted duct - width 300mm Floor-standing duct - width 300mm
Membrane
Insulated material
4 diameter: 57 mm 12 diameter: 1014 mm 4 diameter: 1420 mm 1 diameter: 2026 mm 4 diameter: 814 mm 4 diameter: 714 mm
Set of 1
180 mm
0.28 kg

Colour

Environment

Ip Degree Of Protection	IP55

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	11 cm
Package 1 Length	22 cm

White (RAL 9001)

Package 1 Weight

Contractual warranty

Warranty

12 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile