Product datasheet

Specifications





Kaedra - for modular device - 2 x 18 modules - 448 x 460 mm

10343

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for modular device
Mounting Plate Description	Without mounting plate

Complementary

Enclosure Mounting	Surface
Number Of 18 Mm Modules Per Row	18
Total Number Of 18 Mm Modules	36
Number Of Horizontal Rows	2
Electrical Insulation Class	Class II Double insulation
Provided Equipment	2 marking kit 2 wiring strap
Type Of Front Cover	Transparent Reversible
Power Dissipation In W	47 W
[In] Rated Current	90 A
Type Of Rail	DIN
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	448 mm
Height	460 mm
Depth	160 mm
Internal Depth	88 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)
Targeted Country	Italy

Environment

Standards	IEC 60670	
	IEC 60695-2-1	
	IFC 61439-3	

Fire Resistance	650 °C conforming to IEC 60695-2-1	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK09 conforming to EN 50102	
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013	
Overvoltage Category	II .	
Ambient Air Temperature For Operation	-2560 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.4 cm
Package 1 Width	46.6 cm
Package 1 Length	46.8 cm
Package 1 Weight	3.915 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	18
Package 2 Height	77.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	82.47 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >








Lower Impact Materials Transparency RoHS/REACh

Resource performance



Well-being performance



Rohs Exemption Information



Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations