Product datasheet

Specifications





Kaedra - for plug and socket - 2 openings - 1 x 4 modules

10361

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for plug and socket
Mounting Plate Description	Without mounting plate

Complementary

Enclosure Mounting	Surface
Number Of 18 Mm Modules Per Row	4
Total Number Of 18 Mm Modules	4
Number Of Horizontal Rows	1
Electrical Insulation Class	Class II Double insulation
Number Of Openings Of Interface	2
Number Of Plates	1 for 50 x 50 power outlets
Provided Equipment	1 plate for 50 x 50 power outlet
Type Of Front Cover	Transparent
Power Dissipation In W	6.5 W
[In] Rated Current	63 A
Type Of Rail	DIN
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Base Dimension	65 x 85 mm
Width	98 mm
Height	310 mm
Depth	98.5 mm
Internal Depth	61 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)
Targeted Country	Italy

Environment



Standards	IEC 60695-2-1 IEC 61439-3 IEC 60670
Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-2560 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.400 cm
Package 1 Width	10.700 cm
Package 1 Length	31.500 cm
Package 1 Weight	480.000 g
Unit Type Of Package 2	P12
Number Of Units In Package 2	192
Package 2 Height	120.000 cm
Package 2 Width	80.000 cm
Package 2 Length	77.000 cm
Package 2 Weight	104.160 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Lower Impact Materials Transparency RoHS/REACh

Resource performance



Minimum Percentage Of Recycled Plastic Content

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations