Product datasheet

Specifications





Kaedra - versatil efor power outlet - 1 x 5 modules - 138 x 460 mm

10374

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Versatile enclosure for power outlet
Mounting Plate Description	Slotted

Complementary

Complementary	
Enclosure Mounting	Surface
Number Of 18 Mm Modules Per Row	5
Total Number Of 18 Mm Modules	5
Number Of Horizontal Rows	1
Electrical Insulation Class	Class II Double insulation
Type Of Front Cover	Transparent
Power Dissipation In W	12 W
[In] Rated Current	63 A
Type Of Rail	DIN
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	138 mm
Height	460 mm
Depth	160 mm
Internal Depth	91 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)
Targeted Country	Italy

Environment

Standards	IEC 60695-2-1 IEC 60670 IEC 61439-3
Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529

Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	П
Ambient Air Temperature For Operation	-2560 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.8 cm
Package 1 Width	16.8 cm
Package 1 Length	47.0 cm
Package 1 Weight	1.5 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Lower Impact Materials Transparency RoHS/REACh

Resource performance

Minimum Percentage Of Recycled 27 Plastic Content

Well-being performance

Rohs Exemption Information	Yes
Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations