

Product datasheet

Specifications



Kaedra - for plug and socket - 1 openings - 1 x 4 modules - 1 terminal block

13150

⚠ Discontinued on: 2 Jan 2024

⚠ Discontinued

Main

Range	Kaedra
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for plug and socket
Accessories Included With Enclosure	1 terminal block 4 holes
Mounting Plate Description	Without mounting plate

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	8
Number Of 18 Mm Modules Per Row	4
Total Number Of 18 Mm Modules	4
Number Of Horizontal Rows	1
Electrical Insulation Class	Class II Double insulation
Number Of Openings Of Interface	1
Provided Equipment	1 terminal block 4 holes
Type Of Front Cover	Transparent
Power Dissipation In W	6.5 W
[In] Rated Current	63 A
Number Of Pre-Cutouts Pg Iso	1
Number Of Terminal Blocks	1 with 4 outgoers
Distribution Block Outgoers	2 x 10 mm ² 2 x 16 mm ²
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Base Dimension	65 x 85 mm
Width	98 mm
Height	248 mm
Depth	98.5 mm
Internal Depth	61 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	Door: transparent green Enclosure: light grey (RAL 7035)
--------	---

Environment

Standards	IEC 670 EN 50102 IEC 60439-3 IEC 60529 EN 50262
Fire Resistance	750 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.700 cm
Package 1 Width	9.500 cm
Package 1 Length	25.000 cm
Package 1 Weight	400.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	22.000 cm
Package 2 Width	34.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.600 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	192
Package 3 Height	80.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	96.096 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information