

# Product datasheet

Specifications



## Kaedra - for plug and socket - 8 openings - 1 x 18 modules - 1 terminal block

13157

⚠ Discontinued on: 2 Jan 2024

⚠ Discontinued

### Main

Range	Kaedra
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for plug and socket
Accessories Included With Enclosure	2 plates for push-button controls 1 terminal block 16 holes 2 wiring straps 1 terminal block support 8 plates for 65 x 85 power outlets
Mounting Plate Description	Without mounting plate

### Complementary

Enclosure Mounting	Surface
9 Mm Pitches	36
Number Of 18 Mm Modules Per Row	18
Total Number Of 18 Mm Modules	18
Number Of Horizontal Rows	1
Electrical Insulation Class	Double insulation Class II
Number Of Openings Of Interface	8
Number Of Plates	2 for push-button controls 8 for 65 x 85 power outlets
Provided Equipment	2 wiring strap 8 plate for 65 x 85 power outlet 1 terminal block support 2 plate for push-button control 1 terminal block 16 holes
Type Of Front Cover	Transparent
Power Dissipation In W	34 W
[In] Rated Current	90 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	17
Number Of Terminal Blocks	1 with 16 outgoers
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Base Dimension	90 x 100 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	448 mm
Height	460 mm
Depth	160 mm
Internal Depth	91 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

## Environment

Standards	EN 50102 EN 50262 IEC 670 IEC 60529 IEC 60439-3
Fire Resistance	750 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	47.500 cm
Package 1 Width	46.500 cm
Package 1 Length	17.500 cm
Package 1 Weight	3.650 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	18
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	75.702 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information