Product datasheet

Specifications





Kaedra - for modular device - 1 x 12 modules - 2 terminal blocks

13431

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for modular device
Mounting Plate Description	Without mounting plate

Complementary

· · · · · · · · · · · · · · · · · ·	
Enclosure Mounting	Surface
9 Mm Pitches	24
Number Of 18 Mm Modules Per Row	12
Total Number Of 18 Mm Modules	12
Number Of Horizontal Rows	1
Electrical Insulation Class	Class II Double insulation
Provided Equipment	1 marking kit 1 wiring strap 1 terminal block support 2 terminal block 8 holes
Type Of Front Cover	Transparent Reversible
Power Dissipation In W	24 W
[In] Rated Current	63 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	17
Number Of Terminal Blocks	2 earth / neutral (screw connection) with 8 outgoers
Distribution Block Outgoers	8 x 10 mm ² 8 x 16 mm ²
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	340 mm
Height	280 mm
Depth	160 mm
Internal Depth	88 mm

Colour Door: transparent green
Enclosure: light grey (RAL 7035)

Environment

Standards	IEC 60670 IEC 61439-3	
	EN 50262	
	IEC 60695-2-1	
Fire Resistance	650 °C conforming to IEC 60695-2-1	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK09 conforming to EN 50102	
Environmental Characteristics	UV resistant: class 3 conforming to ISO 4582:2010	
(Uv)	Ultraviolet degradation test conforming to ISO 4892-2:2013	
Overvoltage Category	П	
Ambient Air Temperature For Operation	-2560 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.500 cm
Package 1 Width	30.000 cm
Package 1 Length	36.000 cm
Package 1 Weight	1.978 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	3
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	6.584 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	48
Package 3 Height	120.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	117.344 kg

Contractual warranty

Warranty 12 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Yes



Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations