

Product datasheet

Specifications



Kaedra - for modular device - 3 x 12 modules - 2 terminal blocks

13435

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for modular device
Mounting Plate Description	Without mounting plate

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	24
Number Of 18 Mm Modules Per Row	12
Total Number Of 18 Mm Modules	36
Number Of Horizontal Rows	3
Electrical Insulation Class	Double insulation Class II
Provided Equipment	3 marking kit 3 wiring strap 1 terminal block support 2 terminal block 32 holes
Type Of Front Cover	Transparent Reversible
[In] Rated Current	125 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	17
Number Of Terminal Blocks	2 earth / neutral (screw connection) with 32 outgoers
Distribution Block Outgoers	32 x 10 mm² 32 x 16 mm²
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	340 mm
Height	610 mm
Depth	160 mm
Internal Depth	88 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 60670 IEC 60695-2-1 IEC 61439-3 EN 50262
Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.200 cm
Package 1 Width	36.000 cm
Package 1 Length	62.500 cm
Package 1 Weight	4.550 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	22
Package 2 Height	116.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	109.000 kg

Contractual warranty

Warranty	12 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Lower Impact Materials Transparency RoHS/REACH

Resource performance

✓

Minimum Percentage Of Recycled Plastic Content

27

Well-being performance

✓

Rohs Exemption Information

Yes

✓

Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations