Product datasheet

Specifications

Green Premium[™]



Kaedra - for modular device - 4 x 18 modules - 4 terminal blocks

13437

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for modular device
Mounting Plate Description	Without mounting plate

Complementary

Complementary	
Enclosure Mounting	Surface
9 Mm Pitches	36
Number Of 18 Mm Modules Per Row	18
Total Number Of 18 Mm Modules	72
Number Of Horizontal Rows	4
Electrical Insulation Class	Class II Double insulation
Provided Equipment	4 marking kit 4 wiring strap 2 terminal block support 4 terminal block 32 holes
Type Of Front Cover	Reversible Transparent
Power Dissipation In W	89 W
[In] Rated Current	160 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	17
Number Of Terminal Blocks	4 earth / neutral (screw connection) with 32 outgoers
Distribution Block Outgoers	64 x 10 mm² 64 x 16 mm²
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	448 mm
Height	842 mm
Depth	160 mm
Internal Depth	88 mm

Door: transparent green Enclosure: light grey (RAL 7035)

Environment

Standards	EN 50262 IEC 61439-3 IEC 60670 IEC 60695-2-1
Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	П
Ambient Air Temperature For Operation	-2560 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.000 cm
Package 1 Width	47.000 cm
Package 1 Length	85.000 cm
Package 1 Weight	8.010 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	11
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	100.110 kg

Contractual warranty

Warranty

12 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Lower Impact Materials Transparency RoHS/REACh

Resource performance

Minimum Percentage Of Recycled 24 Plastic Content

Well-being performance

Rohs Exemption Information	Yes
Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations