Product datasheet

Specifications





discrete input module Modicon Quantum - 32 inputs - 115 V AC

140DAI55300C

- () Discontinued on: 31 Mar 2022
- () To be end-of-service on: 31 Dec 2029

① To be discontinued

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	VAC discrete input modules
Software Name	Unity Pro ProWORX 32 Concept
Discrete Input Number	32

Complementary

Group Of Channels	4
Addressing Requirement	2 input words
Discrete Input Voltage	115 V AC
Input Current	11.1 mA at 5763 Hz
	13.2 mA at 4753 Hz
Voltage State 1 Guaranteed	79132 V AC at 5763 Hz
Voltage State 1 Suaranteeu	85132 V AC at 4753 Hz
	05152 V AC at 4755 Hz
Voltage State 0 Guaranteed	020 V AC at 5763 Hz
3	020 V AC at 4753 Hz
Input Impedance	12000 Ohm capacitive at 5763 Hz
	14400 Ohm capacitive at 4753 Hz
Network Frequency Limits	4763 Hz
Maximum Leakage Current	2.1 mA
Absolute Maximum Input	132 V continuous
•	156 V 10 s
	200 V 1 cycle
Response Time	4.90.75 ms x line cycle Off-On
	7.312.3 ms On-Off
Isolation Between Group	1780 Vrms for 1 minute
Isolation Between Group And Bus	1780 Vrms for 1 minute
Bus Current Requirement	250 mA
Maximum Power Dissipation In W	10.9 W
Local Signalling	1 LED (green) for bus communication is present (Active)
5 5	1 LED (red) for external fault detected (F)
	32 LEDs (green) for input status
Marking	CE
Module Format	Standard
Net Weight	0.33 kg

Environment

Protective Treatment	Conformal coating Humiseal 1A33
Standards	CSA C22.2 No 142 UL 508
Product Certifications	cUL FM Class 1 Division 2
Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance To Electromagnetic Fields	10 V/m 802000 MHz conforming to IEC 801-3
Ambient Air Temperature For Operation	060 °C
Ambient Air Temperature For Storage	-4085 °C
Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.3 cm
Package 1 Width	4.5 cm
Package 1 Length	31.2 cm
Package 1 Weight	459.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	2
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.728 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards


Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Product datasheet

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Product datasheet

Connections and Schema

115 Vac Discrete Input Module

Wiring Diagram



N/C Not Connected

NOTE: All inputs in a group must be from the same phase of line input voltage.