



Main

Range	Masterpact
Range of product	Masterpact NW Masterpact NT
Product or component type	Control unit
Trip unit name	Micrologic 5.0
Trip unit technology	Electronic
Range compatibility	Masterpact NT06...16 Masterpact NW08...40 Masterpact NW40b...63
Device application	Distribution
Number of poles	4P 3P
Protected poles description	3t 3t + N/2 4t
Trip unit protection functions	Selective protection
Protection type	for short time short-circuit protection for overload protection (long time) for instantaneous short-circuit protection
Trip unit rating	630 A at 50 °C 800 A at 50 °C 1000 A at 50 °C 1250 A at 50 °C 1600 A at 50 °C 2000 A at 50 °C 2500 A at 50 °C 3200 A at 50 °C 4000 A at 50 °C 5000 A at 50 °C 6300 A at 50 °C
Network type	AC
Network frequency	50/60 Hz
Circuit breaker mounting mode	Fixed Drawout

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Complementary

Long-time pick-up adjustment type Ir (thermal protection)	Adjustable 9 settings
[Ir] long-time protection pick-up adjustment range	0.4...1 x In
Long-time protection delay adjustment type tr	Adjustable 9 settings
[Tr] long-time protection delay adjustment range	0.7...16.6 s at 7.2 x Ir 0.5...24 s at 6 x Ir 12.5...600 s at 1.5 x Ir
Thermal memory	20 mn
Short-time protection pick-up adjustment type lsd	Adjustable 9 settings
[Isd] Short-time protection pick-up adjustment range	1.5...10 x Ir
Short-time protection delay adjustment type tsd	Adjustable
[Tsd] Short-time protection delay adjustment range	0...0.4 s I ² t=off 0.1...0.4 s I ² t=on
Instantaneous protection pick-up adjustment type li	Adjustable 9 settings
[li] instantaneous protection pick-up adjustment range	2...15 x In Off
Earth-leakage protection	Without
Local signalling	3 LEDs (red) for electrical fault 1 LED (red) for internal error

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	170 g
Package 1 Height	7 cm
Package 1 width	8 cm
Package 1 Length	22 cm
Unit Type of Package 2	S03
Number of Units in Package 2	15
Package 2 Weight	3 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P06
Number of Units in Package 3	120
Package 3 Weight	20.4 kg
Package 3 Height	74 cm
Package 3 width	80 cm
Package 3 Length	60 cm

Offer Sustainability

RECh Regulation	RECh Declaration
EU RoHS Directive	Compliant

[EU RoHS Declaration](#)

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
PVC free	Yes

[Contractual warranty](#)

Warranty	18 months
----------	-----------