# **Product datasheet**

Specifications





# voltage release MN - 100..130 V DC/AC 50/60 Hz

47382

#### Main

Range	MasterPacT
Range Of Product	MasterPact NT
	MasterPact NW
	MasterPact NW DC
Device Short Name	MN
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Opening coil
	Undervoltage release
Control Type	Standard
[Uc] Control Circuit Voltage	100130 V AC 50/60 Hz
	100130 V DC
Circuit Breaker Mounting Mode	Fixed
Range Compatibility	Masterpact MasterPact NT
	Masterpact MasterPact NW
	Masterpact MasterPact NW DC

### Complementary

Operating Threshold	0.350.7 x Un opening 0.85 Un closing	
Response Time	40 ms +/- 5 % for MasterPact NT 90 ms +/- 5 % for MasterPact NW	
Supply Holding Power	4.5 VA	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	8.0 cm
Package 1 Length	6.0 cm
Package 1 Weight	174.0 g

#### **Contractual warranty**

Warranty

12 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information