## **Product datasheet**

Specifications





# motor-mechanism - MCH - 200..240 V AC

47466

#### Main

<b>Device Short Name</b>	gear motor MCH
Product Or Component Type	Gear motor mechanism MCH
Device Application	Automatic spring charging
Range Compatibility	Masterpact MasterPact NT circuit breaker
Control Type	Motor mechanism
[Uc] Control Circuit Voltage	200240 V AC 50/60 Hz
Circuit Breaker Mounting Mode	Drawout

### Complementary

Maximum Charging Time	3 s
Maximum Power Consumption In Va	180 VA

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.2 cm
Package 1 Width	12.5 cm
Package 1 Length	18.0 cm
Package 1 Weight	839.0 g

### **Contractual warranty**

Warranty	12 months

## Sustainability Screen Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information