



### Main

|                           |              |
|---------------------------|--------------|
| Range                     | PratiKa      |
| Product or component type | Wander plug  |
| Device short name         | PratiKa plug |
| Plug, socket category     | Low voltage  |
| Poles description         | 3P + E       |
| Network type              | AC           |
| Outlet standard           | Industrial   |

### Complementary

|                                     |  |
|-------------------------------------|--|
| Plug, socket, control station shape | Straight   |
| [In] rated current                  | 63 A   |
| [Ue] rated operational voltage      | 380...415 V                                      |
| Network frequency                   | 50/60 Hz   |
| Ground lug clockwise position       | 6 h  |
| Plug, socket material               | Self-extinguishing engineering polymer housing : |
| Contacts material                   | Nickel plated brass pins :                       |
| Connections - terminals             | Captive screws                                   |
| Cable cross section                 | 6...25 mm <sup>2</sup>                           |
| Cable outer diameter                | 17...31 mm                                       |
| Cable entry                         | Cable gland                                      |
| Thread type                         | Pg 36  |
| Product weight                      | 0.736 kg   |
| Height                              | 265 mm   |
| Width                               | 110 mm   |
| Depth                               | 110 mm   |
| Colour                              | Grey ( RAL 7035 )                                |
| Voltage colour                      | Red  |

### Environment

|           |             |
|-----------|-------------|
| Standards | IEC 60309-1 |
|-----------|-------------|

IEC 60309-2

|                                       |  |
|---------------------------------------|--|
| IP degree of protection               | IP67 conforming to IEC 60529                       |
| IK degree of protection               | IK08 conforming to EN 62262                        |
| Fire resistance                       | 850 °C conforming to IEC 60695-2-11                |
| Relative humidity                     | 50 % ( 40 °C )<br>70 % ( 30 °C )<br>90 % ( 20 °C ) |
| Operating altitude                    | 2000 m   |
| Ambient air temperature for operation | 35 °C ( 86400 s )<br>-25...40 °C                   |

**Contractual warranty**

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|