



Main

Range	PratiKa
Product or component type	Wander socket
Device short name	PratiKa socket
Plug, socket category	Low voltage
Poles description	3P + E
Network type	AC
Outlet standard	Industrial

Complementary

Plug, socket, control station shape	Straight
[In] rated current	63 A
[Ue] rated operational voltage	380...415 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Self-extinguishing engineering polymer housing :
Contacts material	Stainless steel pins : Nickel plated brass sleeves : Stainless steel springs :
Connections - terminals	Captive screws
Cable cross section	6...25 mm ²
Cable outer diameter	17...31 mm
Cable entry	Cable gland
Thread type	Pg 36
Product weight	0.742 kg
Height	110 mm
Width	110 mm
Depth	265 mm
Colour	Grey (RAL 7035)
Voltage colour	Red

Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-1
Relative humidity	50 % (40 °C) 70 % (30 °C) 90 % (20 °C)
Ambient air temperature for operation	35 °C (86400 s) -25...40 °C